



Reduce your energy and water costs by recovering up to **15m³ of hot water per hour!**

Blue Ocean Filtration

Save water and energy in your laundry

The most efficient and reliable system to recycle water in industrial laundries

- ◆ Disk filtration technology to deliver consistent depth filtration down to 115µm
- ◆ Capacity to recover up to 15m³ per hour treating water from multiple washers
- ◆ Automatic self-cleaning triggered by an integrated differential pressure sensor
- ◆ Closed filtration housing to guarantee the highest hygienic standards
- ◆ Stainless steel 1800 liter tanks with level sensors, coned bottom and vortex breakers
- ◆ Possibility to integrate steam injections in the filtrate tank to control the water temperature
- ◆ Fully automatic system to minimize maintenance needs and continuously control the process
- ◆ Complete preassembled and tested unit to minimize installation time and risks
- ◆ All components are enclosed in a compact design with a footprint of 3030 x 1240 mm
- ◆ Magnetic flow meter and temperature sensors to control water and energy savings
- ◆ Central PLC with 7½" full color touch screen and graphic interface
- ◆ Possibility to collect all the removed lint and hair in an Ecolab AquaDrain bag filter
- ◆ Proven technology already used by more than 200 laundries worldwide